# Light Fastness Tester Mercury Tungsten Lamp

To determine the colorfastness and degradation due to the effects of sunlight on textiles.

### **Standard Model**

The standard model is fitted with a 500 watt mercury blended tungsten lamp with presettable timer and time elapsed counter. Can be fitted with type C & D sample holders within which humidity can be controlled using saturated salts.

## **Rapid Light Fastness Tester**

Rapid fade model is fitted with a 400 watt mercury tungsten high power lamp with transformer, presettable timer and time elapsed counter. Can be fitted with type D sample holder.



### Size

Width	Depth	Height	Weight
450 mm	480 mm	480 mm	23 kg

## **Ordering Information**

Light Fastness Tester (Standard)	
Light Fastness Tester (Standard)	
Cylindrical Cell (pack of 50)	
Water-Cooled Cell	
Spare Lamp (Standard)	
Spare Lamp (Rapid Fade)	
Light Fastness Standards	

Standards: BS 1006 UK/TN



#### SDL ATLAS LLC

3934 Airway Drive Rock Hill, SC 29732-9200, USA Telephone: +1 803 329 2110 Facsimile: +1 803 329 2133 Website: www.sdlatlas.com

#### SDL ATLAS LTD.

1/F (South-East) & 2F, Shenjian Mansion, Central District (West), Hi-Tech Park, Nanshan, Shenzhen, 518057, P.R.C. Telephone: +86 (755) 2671 1168 Facsimile: +86 (755) 2671 1337 Website: www.sdlatlas.com

#### SDL ATLAS LTD.

3J, Garment Centre, 576 Castle Peak Road, Kowloon, Hong Kong. Telephone: (852) 3443 4888 Facsimile: (852) 3443 4999 Website: www.sdlatlas.com