


F217A/B/C Rapid Oil Extraction Apparatus

To determine the oil or finish content of wool or synthetic samples by solvent percolation and evaporation. Suitable for fiber, yarn or fabric. Available with 1, 2 or 3 extraction units. Complies with Edana method ERT 155 (needs S217014 large extraction tube fully compliant). Full title of new method is: DETERMINATION OF ACETONE EXTRACTABLE FINISH ON NONWOVENS.

WEIGHT (Model A)	4.4 kg	9.7 lb		
DIMENSIONS (Model A)	Width	Depth	Height	
	170 mm	170 mm	380 mm	
	7 inch	7 inch	15 inch	
STANDARDS	Edana method ERT 155			
ORDERING Info.	F217A	Rapid Oil Extraction Apparatus Single		
	F217B	Rapid Oil Extraction Apparatus Double		
	F217C	Rapid oil Extraction Apparatus Triple		
	F217E	Foil Residue Trays (Pack of 50)		



SDL Atlas, Ltd

PO Box 162, Crown Royal, Shawcross St., Stockport SK1 3JW,
Tel: +44 (0) 161 480 8485 Fax: +44 (0) 161 480 8580
Internet: <http://www.sdlatlas.com>

SDL Atlas, LLC

3934 Airway Drive, Rock Hill, SC 29732, USA
Tel: +1 (803) 329-2110 Fax: +1 (803) 329-2133
Internet: <http://www.sdlatlas.com>

SDL Atlas, Ltd

1/F (South-East) & 2F, Shenjian Mansion, Central District
(West), Hi-Tech Park, Nanshan, Shenzhen, 518057, P.R.C.
Tel: +86 (755) 2671 1168 Fax: +86 (755) 2671 1337
Internet: <http://www.sdlatlas.com.cn>

SDL Atlas, Ltd

3J, Garment Centre, 576 Castle Peak Road, Kowloon, Hong
Kong
Tel: (852) 2173 8611 Fax: (852) 2370 2949
Internet: <http://www.sdlatlas.com>