

Y109A

Quicknit Laboratory Sample Knitting Machine

Quicknit Laboratory Sample Knitting Machine. The Quicknit Machine has been designed with a number of unique features that makes it a user - friendly and economical machine for operators without specific knitting or machine knowledge.

- Industry Standard 3 - 1/2" diameter x 240 needle cylinder, suitable for filament and staple yarns.
- DC motor and gear drive system as used in production machine guarantees long life. Operates on 220v, 50/60hz, single phase for worldwide use.
- Stitch control adjuster allows a wide range of yarn counts to be knitted without changing cylinders.
- Two-finger yarn feed with pneumatic changer allows rapid supply pack-age change from 4-position yarn stand.
- Pneumatic fabric transport and stress - relaxing storage container eliminates expensive and complicated fabric takedown and roll-up systems, allowing very short examples to be knit and cut off for rapid testing.
- Optional automatic oiling system ensures knitting elements are adequately but not excessively lubricated, to reduce maintenance and produce cleaner fabric.
- Comprehensive picture - based instruction allow simple threading operation and maintenance.
- An included tool and consumable parts kit covers all operational requirements.

ELECTRICAL - 220 - 240v, 50 or 60hz, 1 phase, 20amp start-up

AIR REQUIREMENT - Dry, Oil free instrument - quality compressed air, 3/8" line size, minimum 5 bar pressure.

WEIGHT	170kg	375 lb	
DIMENSIONS	Width	Depth	Height
	550 mm	1100 mm	1730 mm
	22 inch	44 inch	68 inch
ORDERING Info.	Y109A	Quicknit Laboratory Sample Knitting Machine	
	Y109AA	Automatic Oiling System	



SDL Atlas, Ltd

PO Box 162, Crown Royal, Shawcross St., Stockport SK1 3JW,
Tel: +44 (0) 161 480 8485 Fax: +44 (0) 161 480 8580
Internet: <http://www.sdlatlas.com>

SDL Atlas, LLC

3934 Airway Drive, Rock Hill, SC 29732, USA
Tel: +1 (803) 329-2110 Fax: +1 (803) 329-2133
Internet: <http://www.sdlatlas.com>

SDL Atlas, Ltd

1/F (South-East) & 2F, Shenjian Mansion, Central District (West), Hi-Tech Park, Nanshan, Shenzhen, 518057, P.R.C.
Tel: +86 (755) 2671 1168 Fax: +86 (755) 2671 1337
Internet: <http://www.sdlatlas.com.cn>

SDL Atlas, Ltd

3J, Garment Centre, 576 Castle Peak Road, Kowloon, Hong Kong
Tel: (852) 2173 8611 Fax: (852) 2370 2949
Internet: <http://www.sdlatlas.com>